

# Ultranitril 485

## DESCRIPTION AND GENERAL PROPERTIES

- **Material** Nitrile
- **Length (cm)** 31
- **Thickness (mm)** 0.34
- **Wrist** Straight cuff
- **Colour/Color** Green
- **Interior finish** Flocked
- **Exterior finish** Embossed texture
- **Size / EAN** 7 8 9 10
- **Packaging** 12 pairs/bag - 72 pairs/carton
- **Complementary information** Guaranteed without silicone



## PERFORMANCE RESULTS

Certification category 3

CE 0334



Dexterity EN 420 : 5/5

Type B



JKOPT



3101X

### Legends

#### EN 388 MECHANICAL HAZARDS



##### PERFORMANCE LEVELS

0-4 0-5 0-4 0-4 A-F (P)  
 └─ Impact protection  
 └─ Cut resistance according to ISO 13997  
 └─ Puncture resistance  
 └─ Tear resistance  
 └─ Blade cut resistance  
 └─ Abrasion resistance

#### EN 407 THERMAL RISKS heat and fire



##### PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4  
 └─ Resistance to large quantities of molten metal  
 └─ Resistance to small drops of molten metal  
 └─ Radiant heat resistant  
 └─ Convective heat resistance  
 └─ Contact heat resistance  
 └─ Burning behaviour

#### CHEMICAL RISKS

##### EN ISO 374-1



Type A  
U V W X Y Z

**A** Methanol  
**B** Acetone  
**C** Acetonitrile  
**D** Dichloromethane  
**E** Carbon Disulfide  
**F** Toluene  
**G** Diethylamine  
**H** Tetrahydrofuran  
**I** Ethyl acetate

##### EN ISO 374-1



Type B  
X Y Z

**J** n-Heptane  
**K** Sodium hydroxide 40%  
**L** Sulphuric acid 96%  
**M** Nitric acid 65%  
**N** Acetic acid 99%  
**O** Ammonia 25%  
**P** Hydrogen peroxide 30%  
**S** Hydrofluoric acid 40%  
**T** Formaldehyde 37%

##### EN ISO 374-1



Type C

#### MICRO-ORGANISMS

##### EN ISO 374-5



Protection against bacteria, fungi

##### EN ISO 374-5



Protection against bacteria, fungi, virus

##### VIRUS



#### COLD HAZARDS

##### PERFORMANCE LEVELS

0-4 0-4 0 or 1  
 └─ Water permeability  
 └─ Contact cold resistance  
 └─ Convective cold resistance



#### RADIOACTIVE CONTAMINATION



#### CUT RESISTANCE

**A1** ≥ 200 G    **A4** ≥ 1500 G    **A7** ≥ 4000 G  
**A2** ≥ 500 G    **A5** ≥ 2200 G    **A8** ≥ 5000 G  
**A3** ≥ 1000 G    **A6** ≥ 3000 G    **A9** ≥ 6000 G

For more details: [www.mapa-pro.com](http://www.mapa-pro.com)

**MAPA**  
PROFESSIONAL

[www.mapa-pro.com](http://www.mapa-pro.com)

## SPECIFIC ADVANTAGES

- Excellent dexterity, due to the suppleness of the glove
- Good grip on slippery objects, due to the embossed exterior finish

## MAIN FIELDS OF USE

### Automotive/mechanical industry

- Machining parts using cutting oil

### Other industries

- Maintenance
- Timber treatment and finishing
- Application of phytosanitary products

### Chemical industry

- Manufacture and application of paints and varnishes

## INSTRUCTIONS FOR USE

### Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the "CE"-type tests.
- Persons sensitized to dithiocarbamates and thiazoles should not use these gloves.
- Put the gloves on dry, clean hands.
- Do not use the gloves in contact with a chemical for a duration in excess of the measured breakthrough time. Refer to the website [www.mapa-pro.com](http://www.mapa-pro.com) or contact the Technical Customer Service - MAPA PROFESSIONNEL ([stc.mapaspontex@mapaspontex.fr](mailto:stc.mapaspontex@mapaspontex.fr)) in order to know this breakthrough time. Use 2 pairs alternatively when in long duration contact with a solvent.
- Turn the cuff end down in order to prevent a hazardous chemical from dripping onto the arm.
- Inspect the gloves for cracks or snags before reusing them.

### Storage conditions

- Store the gloves in their original packaging protected from light, humidity and heat.

### Laundering conditions

- Before taking off the gloves, clean them as appropriate :
- in use with paints, pigments and inks : wipe with a clean cloth dampened with a suitable solvent, and rub over with a dry cloth
- in use with a solvent (alcohols, diluents, etc.) : rub over with a dry cloth
- in use with acids or alkalies : thoroughly rinse the gloves in use with under running water, and rub over with a dry cloth
- Caution : improper use of the gloves or submitting them to any cleaning or laundering process which is not specifically recommended can alter their performance levels.

### Drying conditions

- Ensure the inside of the gloves is dry before putting them on again.

## LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- **UE type certificate or CE type examination certificate** : 0072/014/162/10/18/2079
- **Issued by the notified body nr** : 0075 - CTC - 4 rue Hermann Frenkel - 69367 Lyon cedex 07-France
- **Quality assurance certificat** : 0334 Asqual 14 rue des Reculettes -F-75013 PARIS